



## Rocker button insert 10 A 250 V~ NO contact, 1-pole with N terminal



Spezifikation	Bestell-Nr.	VE	PS	EAN
 with mounting claws	3150 00	1/10/100		4010337038788
 without mounting claws	3870 00	1/10/100		4010337064596

### Merkmale

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

### Technische Daten

Installation depth	
- 3150 00:	32 mm
- 3870 00:	23 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm <sup>2</sup>

### Hinweise

- Can also be connected to be illuminated.

---