

Rocker button 10 A 250 V~ with inscription space (upper housing section) 2-way momentary contact, 1-pole



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|--|-------------|------|----|---------------|
|  grey | 3156 35 | 1/10 | | 4010337124108 |

Merkmale

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Water-protected surface-mounted IP44

Technische Daten

- Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²

Lieferumfang

- The "light", "bell" and "door" symbols are included.