


Rocker indicator switch 16 AX 250 V~ with inscription space and orange LED lighting element 230 V~ Universal 1-way/2-way switch



Spezifikation	Bestell-Nr.	VE	PS	EAN
 grey	3186 30	1		4010337125945

Merkmale

- With orange LED lighting element.
- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Water-protected surface-mounted IP44

Technische Daten

- Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²
- Rated output
- LEDi/CFLi: 100 W

Hinweise

- Can also be connected to be illuminated.

Lieferumfang

- Inscription label "Heating On/Off", "VERWARMING AAN/UIT" is enclosed.
 - Cable entry 2-gang (twin entry) is enclosed.
 - Orange LED lighting element 230 V~ 0.5 mA is included with delivery.
 - Orange LED lighting element 230 V~ 0.5 mA is included with delivery.
-