


Rocker indicator switch insert 10 AX 250 V~ with orange LED lighting element element 230 V~ circuit breaker, 2-pole



Specification	Order No.	Packing unit	PS	EAN
 with mounting claws	3112 00	1/10		4010337038696
 without mounting claws	3822 00	1/10		4010337038702

Features

- Quick mounting (3.5 turns per mounting claw).
- Voltage check possible from the front.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.

Technical data

Installation depth	
- 3112 00:	32 mm
- 3822 00:	23 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm²
Rated output	
- LEDi/CFLi:	100 W

Notes

- Can also be connected to be illuminated by rotating the LED insert by 180°.

Scope of supply

- Orange LED lighting element 230 V~ 0.5 mA is included with delivery.
-