



## Rocker button insert 10 A 250 V~ series button



| Spezifikation  | Bestell-Nr. | VE   | PS | EAN           |
|--|-------------|------|----|---------------|
|  with mounting claws      | 3153 00     | 1/10 |    | 4010337121145 |
|  without mounting claws | 3823 00     | 1/10 |    | 4010337121169 |

### Merkmale

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

### Technische Daten

#### Installation depth

- 3153 00: 32 mm
- 3823 00: 24 mm

#### Connection cross section

- For rigid and flexible conductors up to: 2.5 mm<sup>2</sup>