
© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Pushbutton indicator switch insert 10 AX 250 V~ with orange LED lighting element 230 V~ circuit breaker, 2-pole



Specification	Order No.	Packing unit	PS	EAN
 with mounting claws	3122 00	1		4010337038726
 without mounting claws	3842 00	1		4010337064381

Features

- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- The resulting uniform rocker position gives the electrical installation an organised, premium appearance.
- The aesthetics are greatly enhanced, especially with multiple combinations, for example housing several switches in one frame.

Technical data

Installation depth	
- 3122 00:	32 mm
- 3842 00:	23 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm²
Rated output	
- LEDi/CFLi:	100 W

Notes

- Can also be connected to be illuminated by rotating the LED insert by 180°.

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Scope of supply

- Orange LED lighting element 230 V~ 0.5 mA is included with delivery.

Illustrations are similar and may deviate from originals.