




Rocker switch and rocker button insert 10 A 250 V~ 2-way switch/2-way momentary contact



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|--|-------------|------|----|---------------|
|  with mounting claws | 3139 00 | 1/10 | | 4010337039136 |
|  without mounting claws | 3869 00 | 1 | | 4010337064565 |

Merkmale

- Rocker switch and button in which the left rocker is laid out as a switch and the right rocker is laid out as a push button.
- For switching and colour control of an LED orientation light.
- For controlling motion detectors manually.
- For activating dimmer auxiliary units.
- For controlling switched lighting.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

Technische Daten

| | |
|--|---------------------|
| Installation depth: | 32 mm |
| Connection cross section | |
| - For rigid and flexible conductors up to: | 2.5 mm ² |
| Rated output | |
| - LEDi/CFLi: | 100 W |