



Rocker button insert 10 A 250 V~ NO contact, 1-pole with N terminal



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|--|-------------|----------|----|---------------|
|  with mounting claws | 3150 00 | 1/10/100 | | 4010337038788 |
|  without mounting claws | 3870 00 | 1/10/100 | | 4010337064596 |

Merkmale

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

Technische Daten

| | |
|--|---------------------|
| Installation depth | |
| - 3150 00: | 32 mm |
| - 3870 00: | 23 mm |
| Connection cross section | |
| - For rigid and flexible conductors up to: | 2.5 mm ² |

Hinweise

- Can also be connected to be illuminated.
