




## Rocker button insert 10 A 250 V~ 2-way momentary contact, 2-gang



| Spezifikation  | Bestell-Nr. | VE   | PS | EAN           |
|--|-------------|------|----|---------------|
|  with mounting claws      | 3155 00     | 1/10 |    | 4010337039112 |
|  without mounting claws | 3875 00     | 1/10 |    | 4010337064688 |

### Merkmale

- Can also be used with 1-gang rocker.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

### Technische Daten

|  |                     |
|--|---------------------|
| Installation depth:                        | 32 mm               |
| Connection cross section                   |                     |
| - For rigid and flexible conductors up to: | 2.5 mm <sup>2</sup> |