# GIRA Data sheet



© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

**SCHUKO socket outlet 16 A 250 V~ Screw terminals**



| Specification | Order No. | Packing unit | PS | EAN |
|---|---|---|---|---|
|  cream white glossy | 4180 01 | 1/5 | | 4010337092797 |
|  pure white glossy | 4180 03 | 1/5 | | 4010337092810 |
|  pure white matt | 4180 27 | 1/5 | | 4010337092834 |
|  anthracite | 4180 28 | 1/5 | | 4010337092841 |
|  colour aluminium (lacquered) | 4180 26 | 1/5 | | 4010337092827 |
|  black matt (lacquered) | 4180 005 | 1/5 | | 4010337092780 |
|  grey matt (lacquered) | 4180 015 | 1/5 | | 4010337092803 |
|  stainless steel | 4180 600 | 1 | | 4010337092858 |

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Features**

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.
- Earthed support ring.

---

**Technical data**

| | |
|---|---|
| Installation depth: | 32 mm |
| Conductors: | Rigid and flexible |
| Connection cross section<br>- for conductors from: | 1.5 mm² to 2.5 mm² |

---

**Notes**

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.

---