GIRA Data sheet

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

SCHUKO socket outlet 16 A 250 V~ Screw terminals



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	4180 01	1/5		4010337092797
 pure white glossy	4180 03	1/5		4010337092810
 pure white matt	4180 27	1/5		4010337092834
 anthracite	4180 28	1/5		4010337092841
 colour aluminium (lacquered)	4180 26	1/5		4010337092827
 black matt (lacquered)	4180 005	1/5		4010337092780
 grey matt (lacquered)	4180 015	1/5		4010337092803
 stainless steel	4180 600	1		4010337092858

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.
- Earthed support ring.

Technical data

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm² to 2.5 mm²

Notes

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
