









## SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus) Screw terminals



Spezifikation	Bestell-Nr.	VE	PS	EAN
 cream white glossy	4183 01	1/5		4010337093558
 pure white glossy	4183 03	1/10/100		4010337093572
 pure white matt	4183 27	1/10		4010337093596
 anthracite	4183 28	1/10		4010337093602
 colour aluminium	4183 26	1/5		4010337093589
 black matt	4183 005	1/10		4010337093541
 grey matt	4183 015	1/5		4010337093565
 stainless steel	4183 600	1		4010337093619

## **Merkmale**

- The support ring is earthed in connection with the mounting claws and claw screws.
  - Quick mounting (approx. 3.5 turns per mounting claw).
  - Expanding claws in the housing.
  - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
  - Low installation depth.
  - Large, ergonomically shaped release levers.
  - Sturdy earth bar with solid earthing fingers.
  - Sturdy and corrosion-resistant steel support ring.
  - Shatter-proof thermoplastic base.
  - Earthed support ring.
- 

## **Technische Daten**

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>
Ambient temperature - increased contact protection:	0°C to +45°C

---

## **Hinweise**

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-