









SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus) Screw terminals



Spezifikation	Bestell-Nr.	VE	PS	EAN
 cream white glossy	4183 01	1/5		4010337093558
 pure white glossy	4183 03	1/10/100		4010337093572
 pure white matt	4183 27	1/10		4010337093596
 anthracite	4183 28	1/10		4010337093602
 colour aluminium	4183 26	1/5		4010337093589
 black matt	4183 005	1/10		4010337093541
 grey matt	4183 015	1/5		4010337093565
 stainless steel	4183 600	1		4010337093619

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
 - Quick mounting (approx. 3.5 turns per mounting claw).
 - Expanding claws in the housing.
 - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
 - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
 - Low installation depth.
 - Large, ergonomically shaped release levers.
 - Sturdy earth bar with solid earthing fingers.
 - Sturdy and corrosion-resistant steel support ring.
 - Shatter-proof thermoplastic base.
 - Earthed support ring.
-

Technische Daten

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature - increased contact protection:	0°C to +45°C

Hinweise

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-