© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus) Screw terminals**



| Specification | Order No. | Packing unit | PS | EAN |
|---|---|---|---|---|
| pure white glossy | 4183 70 | 1/5 | | 4010337117759 |
| pure white matt (lacquered) | 4183 72 | 1/5 | | 4010337117766 |
| anthracite (lacquered) | 4183 73 | 1/5 | | 4010337117735 |
| black matt (lacquered) | 4183 74 | 1/5 | | 4010337117773 |
| grey matt (lacquered) | 4183 76 | 1/5 | | 4010337117742 |

**Features**

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

**Technical data**

| | |
|---|---|
| Installation depth: | 32 mm |

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



| | |
|---|---|
| Conductors: | Rigid and flexible |
| Connection cross section<br>- for conductors from: | <br>1.5 mm² to 2.5 mm² |
| Ambient temperature<br>- increased contact protection: | <br>0°C to +45°C |

---

**Notes**

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.

---