




## SCHUKO socket outlet 16 A 250 V~ (IP20) TX\_44



Spezifikation	Bestell-Nr.	VE	PS	EAN
 pure white	4188 66	1/5		4010337093107
 anthracite	4188 67	1/5		4010337093114
 colour aluminium	4188 65	1/5		4010337093091

### Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

### Technische Daten

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>

## Hinweise

- Not suitable for moisture-proof installation, due to protection type IP20.
  - The sealing flange of the frame must be used for installation.
-