








SCHUKO socket outlet 16 A 250 V~ with insert rotated by 30° and increased contact protection (Safety Plus), without mounting claws System 55



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|---|-------------|-----|----|---------------|
|  cream white glossy | 4418 01 | 1/5 | | 4010337094920 |
|  pure white glossy | 4418 03 | 1/5 | | 4010337094944 |
|  pure white matt | 4418 27 | 1/5 | | 4010337094999 |
|  anthracite | 4418 28 | 1/5 | | 4010337095026 |
|  colour aluminium | 4418 26 | 1/5 | | 4010337094982 |
|  black matt | 4418 005 | 1/5 | | 4010337094913 |
|  grey matt | 4418 015 | 1/5 | | 4010337094937 |

Merkmale

- Especially suited for angled plugs.
- Also for use in underfloor systems.
- For screw mounting.

Technische Daten

| | |
|--|--|
| Installation depth: | 32 mm |
| Conductors: | Rigid and flexible |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |
| Ambient temperature - increased contact protection: | 0°C to +45°C |

Hinweise

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
 - Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-