








**SCHUKO socket outlet 16 A 250 V~ with insert rotated by 30° and increased contact protection (Safety Plus), without mounting claws System 55**



Spezifikation	Bestell-Nr.	VE	PS	EAN
 cream white glossy	4418 01	1/5		4010337094920
 pure white glossy	4418 03	1/5		4010337094944
 pure white matt	4418 27	1/5		4010337094999
 anthracite	4418 28	1/5		4010337095026
 colour aluminium	4418 26	1/5		4010337094982
 black matt	4418 005	1/5		4010337094913
 grey matt	4418 015	1/5		4010337094937

## Merkmale

- Especially suited for angled plugs.
- Also for use in underfloor systems.
- For screw mounting.

## Technische Daten

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>
Ambient temperature - increased contact protection:	0°C to +45°C

---

## Hinweise

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
  - Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-