GIRA Data sheet

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

SCHUKO socket outlet 16 A 250 V~ with insert rotated by 30° and increased contact protection (Safety Plus), without mounting claws



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	4418 70	1/5		4010337117841
 pure white matt (lacquered)	4418 72	1/5		4010337117858
 anthracite (lacquered)	4418 73	1/5		4010337117827
 black matt (lacquered)	4418 74	1/5		4010337117865
 grey matt (lacquered)	4418 76	1/5		4010337117834

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.
- Especially suited for angled plugs.
- Also for use in underfloor systems.
- For screw mounting.

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Technical data

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm² to 2.5 mm²
Ambient temperature - increased contact protection:	0°C to +45°C

Notes

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
