










SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus) System 55



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|--|-------------|----------|----|---------------|
|  cream white glossy | 4453 01 | 1/10/100 | | 4010337093718 |
|  cream white glossy | 4755 01 | 1/10 | | 4010337093879 |
|  pure white glossy | 4453 03 | 1/10/100 | | 4010337093732 |
|  pure white glossy | 4755 03 | 1/10 | | 4010337093893 |
|  pure white matt | 4453 27 | 1/10/100 | | 4010337093763 |
|  pure white matt | 4755 27 | 1/10/100 | | 4010337093916 |
|  anthracite | 4453 28 | 1/10/100 | | 4010337093770 |
|  anthracite | 4755 28 | 1/10 | | 4010337093923 |
|  colour aluminium | 4453 26 | 1/10 | | 4010337093756 |

| | | | | |
|---|------------------|----------|----------|---------------|
|  | colour aluminium | 4755 26 | 1/5 | 4010337093909 |
|  | black matt | 4453 005 | 1/10/100 | 4010337093701 |
|  | black matt | 4755 005 | 1/10 | 4010337093862 |
|  | grey matt | 4453 015 | 1/5 | 4010337093725 |
|  | grey matt | 4755 015 | 1/5 | 4010337093886 |
|  | stainless steel | 4453 600 | 1/5 | 4010337093787 |

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technische Daten

| | |
|--|--|
| Installation depth: | 32 mm |
| Conductors: | Rigid and flexible |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |
| Ambient temperature - increased contact protection: | 0°C to +45°C |

Hinweise

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
