




SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus) (IP20) TX_44



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|--|-------------|-----|----|---------------|
|  pure white | 4453 66 | 1/5 | | 4010337093848 |
|  anthracite | 4453 67 | 1/5 | | 4010337093855 |
|  colour aluminium | 4453 65 | 1/5 | | 4010337093831 |

Merkmale

- Earthed support ring.

Technische Daten

| | |
|--|--|
| Installation depth: | 32 mm |
| Connection cross section | |
| - for rigid and flexible conductors for: | 1.5 mm ² to 2.5 mm ² |
| Ambient temperature | |
| - increased contact protection: | 0°C to 45°C |

Hinweise

- Not suitable for moisture-proof installation, due to protection type IP20.
- The sealing flange of the frame must be used for installation.
- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.