© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus) (IP20) TX_44



Specification	Order No.	Packing unit	PS	EAN
 pure white	4453 66	1/5		4010337093848
 anthracite (lacquered)	4453 67	1/5		4010337093855
 colour aluminium (lacquered)	4453 65	1/5		4010337093831

Features

- Earthed support ring.

Technical data

Installation depth:	32 mm
Connection cross section - for rigid and flexible conductors for:	1.5 mm² to 2.5 mm²
Ambient temperature - increased contact protection:	0°C to 45°C

Notes

- Not suitable for moisture-proof installation, due to protection type IP20.
- The sealing flange of the frame must be used for installation.
- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.

Illustrations are similar and may deviate from originals.