






## SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus) Plug terminals



Spezifikation	Bestell-Nr.	VE	PS	EAN
 pure white glossy	4453 70	1/10/100		4010337117636
 pure white matt (lacquered)	4453 72	1/5		4010337117643
 anthracite (lacquered)	4453 73	1/5		4010337117612
 black matt (lacquered)	4453 74	1/5		4010337117650
 grey matt (lacquered)	4453 76	1/5		4010337117629

### Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

### Technische Daten

Installation depth: 32 mm

Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>
Ambient temperature - increased contact protection:	0°C to +45°C

---

## Hinweise

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
  - Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-