




SCHUKO socket outlet 16 A 250 V~with hinged cover TX_44



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|--|-------------|-----|----|---------------|
|  pure white | 4454 66 | 1/5 | | 4010337094128 |
|  anthracite | 4454 67 | 1/5 | | 4010337094135 |
|  colour aluminium | 4454 65 | 1/5 | | 4010337094111 |

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technische Daten

| | |
|--|--|
| Installation depth: | 29 mm |
| Conductors: | Rigid and flexible |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |