






SCHUKO socket outlet 16 A 250 V AC with hinged cover



Spezifikation	Bestell-Nr.	VE	PS	EAN
 pure white glossy	4454 70	1/5		4010337117384
 pure white matt (lacquered)	4454 72	1/5		4010337117391
 anthracite (lacquered)	4454 73	1/5		4010337117360
 black matt (lacquered)	4454 74	1/5		4010337117407
 grey matt (lacquered)	4454 76	1/5		4010337117377

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technische Daten

Installation depth: 32 mm

Conductors: Rigid and flexible

Connection cross section
- for conductors from: 1.5 mm² to 2.5 mm²

Hinweise

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
