© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

SCHUKO socket outlet 16 A 250 V~ with red cover



Specification	Order No.	Packing unit	PS	EAN
 red glossy	4455 108	1/10		4010337096818

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	32 mm
Conductors - Rigid and flexible:	
Connection cross section - for conductors from:	1.5 mm² to 2.5 mm²

Notes

- The bases of the SCHUKO socket outlets are colour coded accordingly.

Illustrations are similar and may deviate from originals.