

SCHUKO socket outlet 16 A 250 V~ with orange cover



Spezifikation	Bestell-Nr.	VE	PS	EAN
 orange glossy	4455 109	1/5		4010337096832

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technische Daten

Installation depth:	32 mm
Conductors	
- Rigid and flexible:	
Connection cross section	
- for conductors from:	1.5 mm ² to 2.5 mm ²

Hinweise

- The bases of the SCHUKO socket outlets are colour coded accordingly.