# GIRA Data sheet



© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

**SCHUKO socket outlet 16 A 250 V~with inscription space System 55**




| Specification | Order No. | Packing unit | PS | EAN |
|---|---|---|---|---|
| cream white glossy | 4457 01 | 1/5 | | 4010337093244 |
| pure white glossy | 4457 03 | 1/5 | | 4010337093268 |
| pure white matt | 4457 27 | 1/5 | | 4010337093329 |
| anthracite | 4457 28 | 1/5 | | 4010337093336 |
| colour aluminium (lacquered) | 4457 26 | 1/5 | | 4010337093312 |
| black matt (lacquered) | 4457 005 | 1/5 | | 4010337093237 |
| grey matt (lacquered) | 4457 015 | 1/5 | | 4010337093251 |
| stainless steel (lacquered) | 4457 600 | 1/5 | | 4010337093343 |

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Features**

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

---

**Technical data**

| | |
|---|---|
| Installation depth: | 29 mm |
| Conductors: | Rigid and flexible |
| Connection cross section<br>- for conductors from: | 1.5 mm² to 2.5 mm² |

---

**Scope of supply**

- Inscription label “EDV” is enclosed.

---