

SCHUKO socket outlet 16 A 250 V~with inscription space with red cover and imprint "WSV" (other safety power supply)



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|--|-------------|-----|----|---------------|
|  red glossy | 4457 108 | 1/5 | | 4010337093299 |

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technische Daten

| | |
|--|--|
| Installation depth: | 29 mm |
| Conductors: | Rigid and flexible |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |

Hinweise

- The bases of the SCHUKO socket outlets are colour coded accordingly.

Lieferumfang

- Inscription label "EDV" is enclosed.
