© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

SCHUKO socket outlet 16 A 250 V~with inscription space System 55



Specification	Order No.	Packing unit	PS	EAN
cream white glossy	4457 01	1/5		4010337093244
pure white glossy	4457 03	1/5		4010337093268
pure white matt	4457 27	1/5		4010337093329
anthracite	4457 28	1/5		4010337093336
colour aluminium (lacquered)	4457 26	1/5		4010337093312
black matt (lacquered)	4457 005	1/5		4010337093237
grey matt (lacquered)	4457 015	1/5		4010337093251
stainless steel (lacquered)	4457 600	1/5		4010337093343

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm² to 2.5 mm²

Scope of supply

- Inscription label “EDV” is enclosed.
