

SCHUKO socket outlet 16 A 250 V~with inscription space System 55



Spezifikation	Bestell-Nr.	VE	PS	EAN
 cream white glossy	4457 01	1/5		4010337093244
 pure white glossy	4457 03	1/5		4010337093268
 pure white matt	4457 27	1/5		4010337093329
 anthracite	4457 28	1/5		4010337093336
 colour aluminium	4457 26	1/5		4010337093312
 black matt	4457 005	1/5		4010337093237
 grey matt	4457 015	1/5		4010337093251
 stainless steel (lacquered)	4457 600	1/5		4010337093343

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
 - Quick mounting (approx. 3.5 turns per mounting claw).
 - Expanding claws in the housing.
 - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
 - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
 - Low installation depth.
 - Large, ergonomically shaped release levers.
 - Sturdy earth bar with solid earthing fingers.
 - Sturdy and corrosion-resistant steel support ring.
 - Shatter-proof thermoplastic base.
-

Technische Daten

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²

Lieferumfang

- Inscription label "EDV" is enclosed.
-