© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

SCHUKO socket outlet 16 A 250 V~ AC with inscription space



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	4457 70	1/5		4010337117254
 pure white matt (lacquered)	4457 72	1/5		4010337117292
 anthracite (lacquered)	4457 73	1/5		4010337117230
 black matt (lacquered)	4457 74	1/5		4010337117308
 grey matt (lacquered)	4457 76	1/5		4010337117247

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Technical data

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm² to 2.5 mm²

Notes

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.

Scope of supply

- Inscription label “EDV” is enclosed.
