








SCHUKO socket outlet 16 A 250 V~ with inscription space and increased contact protection (Safety Plus) System 55



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|---|-------------|-----|----|---------------|
|  cream white glossy | 4462 01 | 1/5 | | 4010337093367 |
|  pure white glossy | 4462 03 | 1/5 | | 4010337093381 |
|  pure white matt | 4462 27 | 1/5 | | 4010337093404 |
|  anthracite | 4462 28 | 1/5 | | 4010337093411 |
|  colour aluminium | 4462 26 | 1/5 | | 4010337093398 |
|  black matt | 4462 005 | 1/5 | | 4010337093350 |
|  grey matt | 4462 015 | 1/5 | | 4010337093374 |

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technische Daten

| | |
|--|--|
| Installation depth: | 29 mm |
| Conductors: | Rigid and flexible |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |
| Ambient temperature - increased contact protection: | 0°C to +45°C |

Hinweise

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-

Lieferumfang

- Inscription label "EDV" is enclosed.
-