

SCHUKO socket outlet 16 A 250 V~ with inscription space and increased contact protection (Safety Plus) System 55



Spezifikation	Bestell-Nr.	VE	PS	EAN
 cream white glossy	4462 01	1/5		4010337093367
 pure white glossy	4462 03	1/5		4010337093381
 pure white matt	4462 27	1/5		4010337093404
 anthracite	4462 28	1/5		4010337093411
 colour aluminium	4462 26	1/5		4010337093398
 black matt	4462 005	1/5		4010337093350
 grey matt	4462 015	1/5		4010337093374

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technische Daten

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature - increased contact protection:	0°C to +45°C

Hinweise

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.

Lieferumfang

- Inscription label "EDV" is enclosed.
-