




**SCHUKO socket outlet 16 A 250 V~ with inscription space and increased contact protection (Safety Plus) (IP20) TX\_44**

Spezifikation	Bestell-Nr.	VE	PS	EAN
 pure white	4462 66	1/5		4010337093497
 anthracite	4462 67	1/5		4010337093503
 colour aluminium	4462 65	1/5		4010337093480

**Merkmale**

- Earthed support ring.

**Technische Daten**

Installation depth:	32 mm
Connection cross section	
- for rigid and flexible conductors for:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>
Ambient temperature	
- increased contact protection:	0°C to 45°C

**Hinweise**

- Not suitable for moisture-proof installation, due to protection type IP20.
- The sealing flange of the frame must be used for installation.
- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.

## Lieferumfang

- Inscription label "EDV" is enclosed.

---