






## SCHUKO socket outlet 16 A 250 V~ with inscription space and increased contact protection (Safety Plus)



| Spezifikation   | Bestell-Nr. | VE  | PS | EAN           |
|---|-------------|-----|----|---------------|
|  pure white glossy             | 4462 70     | 1/5 |    | 4010337117339 |
|  pure white matt (lacquered) | 4462 72     | 1/5 |    | 4010337117346 |
|  anthracite (lacquered)      | 4462 73     | 1/5 |    | 4010337117315 |
|  black matt (lacquered)      | 4462 74     | 1/5 |    | 4010337117353 |
|  grey matt (lacquered)       | 4462 76     | 1/5 |    | 4010337117322 |

### Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

### Technische Daten

Installation depth: 32 mm

|  |  |
|--|--|
| Conductors:  | Rigid and flexible                         |
| Connection cross section<br>- for conductors from: | 1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup> |

---

## Hinweise

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
  - Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
- 

## Lieferumfang

- Inscription label "EDV" is enclosed.
-