









SCHUKO socket outlet 16 A 250 V~ without mounting claws System 55



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|---|-------------|----------|----|---------------|
|  cream white glossy | 4466 01 | 1/10 | | 4010337095088 |
|  pure white glossy | 4466 03 | 1/10 | | 4010337095101 |
|  pure white matt | 4466 27 | 1/10/100 | | 4010337095125 |
|  anthracite | 4466 28 | 1/10/100 | | 4010337095132 |
|  colour aluminium | 4466 26 | 1/10 | | 4010337095118 |
|  black matt | 4466 005 | 1/10/100 | | 4010337095071 |
|  grey matt | 4466 015 | 1/5 | | 4010337095095 |
|  stainless steel | 4466 600 | 1/10 | | 4010337095149 |

Merkmale

- Quick mounting (approx. 3.5 turns per mounting claw).
 - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
 - Low installation depth.
 - Large, ergonomically shaped release levers.
 - Sturdy earth bar with solid earthing fingers.
 - Sturdy and corrosion-resistant steel support ring.
 - Shatter-proof thermoplastic base.
-

Technische Daten

| | |
|--|--|
| Installation depth: | 29 mm |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |
