© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

SCHUKO socket outlet 16 A 250 V~ without mounting claws System 55



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	4466 01	1/10		4010337095088
 pure white glossy	4466 03	1/10		4010337095101
 pure white matt	4466 27	1/10/100		4010337095125
 anthracite	4466 28	1/10/100		4010337095132
 colour aluminium (lacquered)	4466 26	1/10		4010337095118
 black matt (lacquered)	4466 005	1/10/100		4010337095071
 grey matt (lacquered)	4466 015	1/5		4010337095095
 stainless steel	4466 600	1/10		4010337095149

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Features

- Quick mounting (approx. 3.5 turns per mounting claw).
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	29 mm
Connection cross section	
- for conductors from:	1.5 mm² to 2.5 mm²
