









## SCHUKO socket outlet 16 A 250 V~ without mounting claws System 55



Spezifikation	Bestell-Nr.	VE	PS	EAN
 cream white glossy	4466 01	1/10		4010337095088
 pure white glossy	4466 03	1/10		4010337095101
 pure white matt	4466 27	1/10/100		4010337095125
 anthracite	4466 28	1/10/100		4010337095132
 colour aluminium	4466 26	1/10		4010337095118
 black matt	4466 005	1/10/100		4010337095071
 grey matt	4466 015	1/5		4010337095095
 stainless steel	4466 600	1/10		4010337095149

## Merkmale

- Quick mounting (approx. 3.5 turns per mounting claw).
  - Expanding claws in the housing.
  - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
  - Low installation depth.
  - Large, ergonomically shaped release levers.
  - Sturdy earth bar with solid earthing fingers.
  - Sturdy and corrosion-resistant steel support ring.
  - Shatter-proof thermoplastic base.
- 

## Technische Daten

Installation depth:	29 mm
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>

---