

SCHUKO socket outlet 16 A 250 V~ without mounting claws Gira F100



Spezifikation	Bestell-Nr.	VE	PS	EAN
 pure white glossy	4466 70	1/10		4010337117896

Merkmale

- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technische Daten

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²