






SCHUKO socket outlet 16 A 250 V~ without mounting claws



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|---|-------------|------|----|---------------|
|  pure white glossy | 4466 70 | 1/10 | | 4010337117896 |
|  pure white matt (lacquered) | 4466 72 | 1/5 | | 4010337117902 |
|  anthracite (lacquered) | 4466 73 | 1/5 | | 4010337117872 |
|  black matt (lacquered) | 4466 74 | 1/5 | | 4010337117919 |
|  grey matt (lacquered) | 4466 76 | 1/5 | | 4010337117889 |

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technische Daten

Installation depth: 32 mm

| | |
|--|--|
| Conductors: | Rigid and flexible |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |

Hinweise

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
