


SCHUKO socket outlet 16 A 250 V~ without mounting claws System 70



Spezifikation	Bestell-Nr.	VE	PS	EAN
 pure white glossy	4466 70	1/10		4010337117896
 pure white matt (lacquered)	4466 72	1/5		4010337117902
 anthracite (lacquered)	4466 73	1/5		4010337117872
 black matt (lacquered)	4466 74	1/5		4010337117919
 grey matt (lacquered)	4466 76	1/5		4010337117889

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technische Daten

Installation depth: 32 mm

Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²

Hinweise

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
