









## Socket outlet with earth pin 16 A 250 V~ and increased contact protection (Safety Plus) System 55



Spezifikation	Bestell-Nr.	VE	PS	EAN
 cream white glossy	4485 01	1/5		4010337095668
 pure white glossy	4485 03	1/10/100		4010337095682
 pure white matt	4485 27	1/10		4010337095712
 anthracite	4485 28	1/10		4010337095729
 colour aluminium	4485 26	1/10		4010337095705
 black matt	4485 005	1/10		4010337095651
 grey matt	4485 015	1/5		4010337095675
 stainless steel	4485 600	1/5		4010337095736

## **Merkmale**

- With plug terminals.
  - The support ring is earthed in connection with the mounting claws and claw screws.
  - Quick mounting (approx. 3.5 turns per mounting claw).
  - Expanding claws in the housing.
  - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
  - Low installation depth.
  - Large, ergonomically shaped release levers.
  - Sturdy earth bar with solid earthing fingers.
  - Sturdy and corrosion-resistant steel support ring.
  - Shatter-proof thermoplastic base.
- 

## **Technische Daten**

Installation depth:	29 mm
Replaces fully compatible 0485 ...:	
Connection cross section	
- for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>
Ambient temperature	
- increased contact protection:	0°C to +45°C

---

## **Hinweise**

- Approved in accordance with NF C 61-314:2017.
  - Approved in accordance with NBN C 61-112-1:2017.
  - Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-