

## Socket outlet with earth pin 16 A 250 V~ and increased contact protection (Safety Plus) System 55



| Spezifikation                                                                                         | Bestell-Nr. | VE       | PS | EAN           |
|-------------------------------------------------------------------------------------------------------|-------------|----------|----|---------------|
|  cream white glossy  | 4485 01     | 1/5      |    | 4010337095668 |
|  pure white glossy | 4485 03     | 1/10/100 |    | 4010337095682 |
|  pure white matt   | 4485 27     | 1/10     |    | 4010337095712 |
|  anthracite        | 4485 28     | 1/10     |    | 4010337095729 |
|  colour aluminium  | 4485 26     | 1/10     |    | 4010337095705 |
|  black matt        | 4485 005    | 1/10     |    | 4010337095651 |
|  grey matt         | 4485 015    | 1/5      |    | 4010337095675 |
|  stainless steel   | 4485 600    | 1/5      |    | 4010337095736 |

## Merkmale

- With plug terminals.
- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

---

## Technische Daten

|                                     |                                            |
|-------------------------------------|--------------------------------------------|
| Installation depth:                 | 29 mm                                      |
| Replaces fully compatible 0485 ...: |                                            |
| Connection cross section            |                                            |
| - for conductors from:              | 1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup> |
| Ambient temperature                 |                                            |
| - increased contact protection:     | 0°C to +45°C                               |

---

## Hinweise

- Approved in accordance with NF C 61-314:2017.
  - Approved in accordance with NBN C 61-112-1:2017.
  - Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-