








## SCHUKO socket outlet 16 A 250 V~ with hinged cover, inscription space and increased contact protection (Safety Plus) System 55



Spezifikation	Bestell-Nr.	VE	PS	EAN
 cream white glossy	4557 01	1/5		4010337094258
 pure white glossy	4557 03	1/5		4010337094265
 pure white matt	4557 27	1/5		4010337094296
 anthracite	4557 28	1/5		4010337094302
 colour aluminium	4557 26	1/5		4010337094289
 black matt	4557 005	1/5		4010337094241
 grey matt	4557 015	1/5		4010337094319

### Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

## Technische Daten

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>
Ambient temperature - increased contact protection:	0°C to +45°C

---

## Hinweise

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
- 

## Lieferumfang

- Inscription label "EDV" is enclosed.
-