








SCHUKO socket outlet 16 A 250 V~ with hinged cover and increased contact protection (Safety Plus) Screw terminals



| Spezifikation | Bestell-Nr. | VE | PS | EAN |
|---|-------------|-----|----|---------------|
|  cream white glossy | 4754 01 | 1/5 | | 4010337114154 |
|  pure white glossy | 4754 03 | 1/5 | | 4010337114178 |
|  pure white matt | 4754 27 | 1/5 | | 4010337114192 |
|  anthracite | 4754 28 | 1/5 | | 4010337114208 |
|  colour aluminium | 4754 26 | 1/5 | | 4010337114185 |
|  black matt | 4754 005 | 1/5 | | 4010337114147 |
|  grey matt | 4754 015 | 1/5 | | 4010337114161 |

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technische Daten

| | |
|--|--|
| Installation depth: | 29 mm |
| Conductors - Rigid and flexible: | |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |

Hinweise

- Cover frames (1-gang to 5-gang) from the Standard 55, Gira E1 and Gira E2 design lines in combination with the sealing kit also suitable for the mounting of flush-mounted SCHUKO socket outlets with hinged cover in accordance with the IP44 protection rating.
 - Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-