









**SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus) without mounting claws**



| Spezifikation  | Bestell-Nr. | VE       | PS | EAN           |
|--|-------------|----------|----|---------------|
|  cream white glossy   | 4453 01     | 1/10/100 |    | 4010337093718 |
|  cream white glossy | 4755 01     | 1/10     |    | 4010337093879 |
|  pure white glossy  | 4453 03     | 1/10/100 |    | 4010337093732 |
|  pure white glossy  | 4755 03     | 1/10     |    | 4010337093893 |
|  pure white matt    | 4453 27     | 1/10/100 |    | 4010337093763 |
|  pure white matt    | 4755 27     | 1/10/100 |    | 4010337093916 |
|  anthracite         | 4453 28     | 1/10/100 |    | 4010337093770 |
|  anthracite         | 4755 28     | 1/10     |    | 4010337093923 |
|  colour aluminium   | 4453 26     | 1/10     |    | 4010337093756 |

|   |                  |          |          |               |
|---|------------------|----------|----------|---------------|
|    | colour aluminium | 4755 26  | 1/5      | 4010337093909 |
|    | black matt       | 4453 005 | 1/10/100 | 4010337093701 |
|    | black matt       | 4755 005 | 1/10     | 4010337093862 |
|    | grey matt        | 4453 015 | 1/5      | 4010337093725 |
|    | grey matt        | 4755 015 | 1/5      | 4010337093886 |
|  | stainless steel  | 4453 600 | 1/5      | 4010337093787 |

## Merkmale

- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

## Technische Daten

|                                 |  |
|---------------------------------|--|
| Installation depth:             | 29 mm                                      |
| Conductors:                     | Rigid and flexible                         |
| Connection cross section        |  |
| - for conductors from:          | 1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup> |
| Ambient temperature             |  |
| - increased contact protection: | 0°C to +45°C                               |

## Hinweise

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.

---