

SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus) without mounting claws



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	4755 01	1/10		4010337093879
 pure white glossy	4755 03	1/10		4010337093893
 pure white matt	4755 27	1/10/100		4010337093916
 anthracite	4755 28	1/10		4010337093923
 colour aluminium (lacquered)	4755 26	1/5		4010337093909
 black matt (lacquered)	4755 005	1/10		4010337093862
 grey matt (lacquered)	4755 015	1/5		4010337093886

Features

- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature - increased contact protection:	0°C to +45°C

Notes

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-