

Pushbutton sensor 4.95, 24 V 4-gang



Specification	Order No.	Packing unit	PS	EAN
 white	5054 003	1		4010337074922
 anthracite	5054 028	1		4010337074939

Features

- Pushbutton sensor 4.95 for connection to 24 V control systems.
- Operating surface made of high-quality three-millimetre thick real material (glass, stainless steel, aluminium).
- Two white status LEDs per rocker.
- Measurement of the room temperature with integrated temperature sensor (PT1000).

Technical data

Button

- Rated voltage: AC/DC 24 V SELV
- Current capacity: 20 mA per button
- Output resistance: 880 Ω

LED

- Rated voltage: DC 24 V SELV
- Current consumption: approx. 1 mA per LED

Temperature sensor: PT1000, class B

Protection class: III

Installation depth: 16 mm

Ambient temperature: -5 °C to +45 °C

Notes

- Suitable for SELV circuits only.
 - Professional inscription by the Gira inscription service www.beschriftung.gira.de.
 - The pushbutton sensor is delivered with a program-neutral start-up rocker. The suitable rocker set for the switch range must be ordered separately.
-