


eNet wireless hand-held transmitter, 4-gang



Spezifikation	Bestell-Nr.	VE	PS	EAN
 anthracite	5354 10	1		4010337774099

Merkmale

- Two buttons belong to each channel.
- Each pair of buttons can be set as channel or scene function.
- Status LED.
- Battery-operated device.

Can be set with eNet server:

- Fully encrypted wireless transmission (AES CCM) from eNet Server software version 2.0.
- Signalling of the transmission status can be switched off.
- Operation locks.
- All-On or All-Off scenes, threshold value scenes, and individual scenes can be configured.
- Configuration of scene button using eNet SMART HOME App (if-then rules) to trigger actions, scenes and timers.
- Device software update.

Technische Daten

Rated voltage:	DC 3 V
Battery	
- Type:	CR 2450N
- UN no.:	3091
Dimensions	
- W x H x D:	53 x 93 x 15,5 mm

Hinweise

- Batteries are consumables and must be replaced regularly. Please observe the regulations on the disposal of used batteries.

Lieferumfang

- Batteries are included with delivery.
