









System 3000 blind timer and timer Display System 55



Spezifikation	Bestell-Nr.	VE	PS	EAN
 cream white glossy	5366 01	1/5		4010337027430
 pure white glossy	5366 03	1/5		4010337027447
 pure white matt	5366 27	1/5		4010337027461
 anthracite	5366 28	1/5		4010337027478
 colour aluminium	5366 26	1/5		4010337027454
 black matt	5366 005	1/5		4010337037484
 grey matt	5366 015	1/5		4010337087243
 stainless steel (lacquered)	5366 600	1/5		4010337027485

Merkmale

- Operation via capacitive sensor surface.
 - Fast programming for adopting the current time as the programmed movement time/switching time.
 - Automatic summer/winter time switchover, deactivatable.
 - Switching at sunrise or sunset (astro function) adjustable for 18 countries.
 - Astro time for sunrise and sunset can be individually adjusted by ± 2 hours.
 - The blocking function blocks operation of the auxiliary unit and deactivates automatic mode.
 - The display turns off after 2 minutes, permanent display of time is possible.
 - Programming one raising and one lowering time or two switch-on and switch-off times for weekdays (Mon-Fri) and for the weekend (Sat+Sun).
-

Technische Daten

Accuracy

- Per month: ± 10 s

Power reserve: approx. 4 h

Ambient temperature: -5°C to $+45^{\circ}\text{C}$
